

**EasiDoser™
ADE/003-1LV
Automatic Dosing & Dispensing System**



Properties

Enclosure & Pump Housing: ABS

Motor/Gearbox: Metal, Copper & Acetyl

PCB: Electronic Components, LCD Display

Spigots & Tubing: Polypropylene & Santoprene

Other Parts: Stainless Steel bracket & pins

Flow rate: 12-45 ml per minute using 1.8 mm bore tube
40-60 ml per minute using 3.2 mm bore tube
65-275 ml per minute using 4.6 mm bore tube
95-375 ml per minute using 6.2 mm bore tube

Supply Voltage: 230V AC 50Hz Mains plug Fuse: 1A

Motor / Gearbox: 12V DC

Machine Signal: 12-24V DC – via opto isolator
12-230V AC – via opto isolator

PCB Fuse: 1AT (5 x 20mm)

Dimensions: 18 x 15.5 x 9 cm

Net weight: 1.55kg

Fixing: At eye level for ease of access and visibility of LCD display.

Country of origin: GB

HS commodity code: 84135040



Product Technical Data Sheet

Description

The EasiDoser™ is a microprocessor-controlled dosing and dispensing control system which is capable of controlling the operation of one peristaltic pump in order to dispense and dose precise quantities of fluids for cleaning or sanitisation purposes. Typical applications include the dispensing of detergent, bleach, acid and/or alkaline for sanitisation purposes as well as the mixing and dilution of udder health chemicals for teat disinfection applications.

The device has an LCD display and keypad on the front of the unit for ease of set up and for programming the pump run time and pump speed; the LCD display also shows relevant information when the unit is running and can be used to access performance data.

Depending how the unit is programmed, the EasiDoser™ will activate when the circuit receives a 12-230V AC or 12-24V DC machine signal through the Opto Isolator (Automatic Mode), or closed contact to one of the trigger inputs (Direct Mode). Also, it can be used for manual dosing and this is activated by pressing a button on the keypad (Manual Mode).

Features

- A combination of time and speed control enables the amount of product dispensed to be determined both by reference to pump speed and run time for accurate dosing.
 - Pump Run Time adjustable from 1 to 5.00 minutes.
 - Pump Speed Control adjustable from 50% to 100%.
 - Pump Start Delay adjustable from 0 to 30 seconds.
- Option of setting a time delay before initiating the pump.
- The unit has a 'Pump Inhibit' or 'Lock-out' safety feature which prevents consecutive dispensing of chemicals where excessive dosing could be a hazard. This is adjustable from 0 to 30 minutes.
- Data logging facility to record and display performance data, including cumulative run time and cumulative chemical consumption.
- Data logging feature includes monitoring of peristaltic tube run time to alert when tubes need replacing.
- Pump calibration is made via the LCD display and keypad.
- Password protected keypad for security.
- Includes low level alarm feature to warn when chemical levels are running low – appropriate lance assemblies can be purchased separately.
- Available with a range of plugs to suit local markets.